

Project _____
Item _____
Quantity _____
CSI Section 11400
Approved _____
Date _____

GAFPTP Pass-Thru

Specification Line® Pass-Thru Freezer

Models

- | | |
|-------------------------------------|-------------------------------------|
| ☐ GAFPT1P-S | ☐ GAFPT2P-S |
| ☐ GAFPT1P-SH | ☐ GAFPT2P-SH |



GAFPT1P-S

Standard Features

- GreenGenius™ R290 top mount refrigeration system featuring TXV expansion valve and hot gas condensate removal
- easyTouch Control with remote monitoring capability
- Digital exterior temperature display with high/low temp visual alarms
- Energy saving LED interior light
- Removable side louver
- Accommodates full size sheet pans
- Raised ABS interior door liner
- Smart door hinge that auto closes up to 90° and stays open past 90°
- Patented, lifetime warranty integral door handle
- Energy efficient door gasket – removable without tools
- Door locks
- 5" locking casters shipped loose for field installation
- 10' cord and plug attached
- Stainless steel exterior front, sides & interior
- Field rehingable doors - full height doors only
- Stainless steel pilaster with shelf clips
- 3 shelves per section
- Chrome standard
- 115V / 60C / 1 P Standard
- Three year parts and labor warranty and an additional 2 year compressor parts warranty.

Options & Accessories

- 6" Stainless steel feet
- 6" Casters (all locking)
- 6" Stainless Steel flanged feet
- Additional chrome shelves
- Stainless steel shelves
- S/S finish door liner
- Tray/Pan Slides – various
- Utility base
- Kick plate
- Laminate – front, ends, shroud
- Heat shield end – max temp 400 degrees
- Trim strips
- Foot Pedal Door Opener


Specifications

Refrigeration system: All components are mounted to the top cabinet ceiling, outside the food zone and are assembled as one piece and can be removed as one piece. Environmentally friendly R290 refrigerant is used. System has the capability of maintaining between -5°F and 0°F in heavy use food service operations. Refrigerant is metered using a highly responsive thermostatic expansion valve. System is controlled using an electronic temperature control, which provides improved pull down times, reducing compressor cycling and longer compressor life with lower energy consumption. Control system uses adaptive defrost to assure evaporator coil is free of ice and operating at optimum efficiency. Evaporator condensate is elimi-


nated using an energy efficient hot gas system. Units are completely insulated with high density foamed in place environmentally friendly, Kyoto Protocol Compliant, Non ODP (Ozone Depletion Potential), Non GWP (Global Warming Potential) polyurethane.




GAFPTP Pass-Thru




TYP. LEFT
END VIEW






GAFPT1P-S




GAFPT2P-S




SECTION
VIEW




TYP. LEFT
END VIEW



GAFPT1P-SH



GAFPT2P-SH



SECTION
VIEW

Specifications									
Model	V/Hz/Ph	Amps	Volume Cu. Ft.	SHELF CAPACITY SQ. FT.	No. of Shelves	Unit H.P.	Btu/Hr System Cap	Ship Weight	Nema Plug
GAFPT1P-S GAFPT1P-SH	115/60/1	7.2	23	12.12	3	0.55	1968	452	5-15P
GAFPT2P-S GAFPT2P-SH	115/60/1	10	50	26.5	6	(2X)0.55	3936	682	5-15P

Welbilt reserves the right to make changes to the design or specifications without prior notice.